



Pass and Seymour
1400 Series Cable Reel with Flying Lead 25A, 10 AWG, 60 ft For Lift/Drag Applications
Part No. CR14L103N60F25



The 1400 Series Industrial Cable Reels are the professionals choice for demanding industrial applications where reliability and versatility are paramount. Made in the USA with a minimum of components, these reels are ideal for assembly and fabrication work areas, Class A/C overhead cranes and hoists, schools and theaters, and much more.

Features & Benefits

Made in USA	Steel frame construction, black thermoplastic slip ring cover, yellow powder-coat finish
NEMA 4 rated enclosure	UL and CSA Listed

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007206043	Country Of Origin	United States
Features	Lift/Drag, Retractable	Application Sector	Commercial, Data Center, Education, Industrial
Warranty Type	1-Year	Type	Cable Reel

Technical Information

Cord Length	25 ft	Amperage	25 A
Number of Conductors	3	Indoor/Outdoor	Both
Mobile End	Flying Lead	Operating Temperature	22°-194°F