



Pass and Seymour
1000 Series Cable Reel with Quad RB, 20 Amp, 12 AWG, 50 ft
Part No. CRCD123G50R20



1000 Series Cable Reel with Quad RB, 20A, 12 AWG, 50 ft

Features & Benefits

Made in USA	Black molded nylon construction with reinforced steel frame
Rated for indoor use	cULus Listed

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007198539	Country Of Origin	United States
Features	Removable Base, Retractable	Application Sector	Commercial, Data Center, Education, Industrial
Warranty Type	2-Year	Type	Cable Reel

Technical Information

Wire Gauge	12 AWG	Cord Length	50 ft
Amperage	20 A	Number of Conductors	3
Indoor/Outdoor	Indoor	Mobile End	Quad Receptacle Box
Operating Temperature	22°-194°F	Voltage	125.0 V