

Turnlok® Receptacle 3-Wire 30A 125V Corrosion Resistant, Yellow



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.:

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

### Dimensions

Product Width US	1.61 in	Product Depth US	1.28 in
Product Height US	2.37 in		

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Number of Wires	3	Amperage	30 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Wire Size	18 - 10 AWG
-----------------	-------------	-----------	-------------

---

Voltage	125.0 V
---------	---------

---