



Pass and Seymour  
50A 125/250V California Standard Single Receptacle, 3-Pole 4-Wire, Black  
Part No. CS6369



Receptacle California Standard Style 50A 125/250V Turnlok®

Features & Benefits

Quality Materials, durability, and time-tested design

140 joules of energy absorption in each of the three modes.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 498

Dimensions

Product Width US	1.98 in	Product Depth US	1.08 in
Product Height US	3.28 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	68837
------------	-----	-----------------	-------

Technical Information

Phase	3	Number of Wires	4
Amperage	50 A	Number of Poles	3-Way
Wire Size	18 - 0 AWG	Voltage	125/250 V