



Pass and Seymour
Hard Use Specification Grade Switch, Light Almond
Part No. CSB15AC2LA



Construction 2-Pole Switch, Back and Side-Wire, 15A 120/277V.

Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007126136
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 20, FEDSPEC		

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Contact Rating	15Amp, 120/277Vac	Closed Contact Resistance	Toggle
Amperage	15 A	Number of Poles	Double Pole
Wire Size	#14 - #10 AWG	Wattage	2 W