



Pass and Seymour
Hard Use Specification Grade Switch, White
Part No. CSB15AC4W

Construction 4-Way Switch, Back and Side-Wire, 15A 120/277V.



Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 20		

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
------------------	---------	------------------	----------

Product Height US	2.375 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Technical Information

Contact Rating	15amp, 120/277vac	Closed Contact Resistance	Toggle
----------------	-------------------	---------------------------	--------

Amperage	15 A	Number of Poles	4-Way
----------	------	-----------------	-------

Wattage	4 W	Voltage	120.0 V
---------	-----	---------	---------
