



Construction 1-Pole Switch, Back and Side-Wire, 20A 120/277V.

## Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |                    |              |
|-------------------|----------------|--------------------|--------------|
| Product Line      | Pass & Seymour | Color              | Brown        |
| Finish            | Matte          | UPC Number         | 785007126051 |
| Country Of Origin | Mexico         | Application Sector | Commercial   |
| Standard          | UL20, FEDSPEC  | Type               | Switch       |

### Dimensions

|                                       |                     |                  |               |
|---------------------------------------|---------------------|------------------|---------------|
| Product Width US                      | 1.32 in             | Product Depth US | 1.073 in      |
| Product Height US                     | 3.281 in            |                  |               |
| Listing Agencies / 3rd Party Agencies |                     |                  |               |
| cULus ListingNumber                   | 140597              | cULus Listed     | Yes           |
| Technical Information                 |                     |                  |               |
| Contact Rating                        | 20 Amp, 120/277 VAC | Amperage         | 20 A          |
| Number of Poles                       | Single Pole         | Wire Size        | #14 - #10 AWG |
| Voltage                               | 120.0 V             |                  |               |