



Wiremold  
Field Wired deQuorum Single-Flip Up Unit  
Part No. DQFF20BK



Field wired unit includes one (1) 20A black tamper-resistant duplex receptacle. Comes with a black powder coat finish.

## Features & Benefits

**Sleek, Attractive Design:** Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

**Tamper-Resistant Receptacles:** Meets 2011 NEC Tamper-Resistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

**New Soft Opening Cover Mechanism:** Opening and closing the cover is quieter and easier with a more professional feel.

**Expanded Configuration Options:** Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

**UL Spill Water Protection:** Meets or exceeds UL 111 - Outline of Investigation for Multioutlet Assemblies. Eliminates risk of shock or short circuiting due to moisture entering device.

**USB Charging Capability:** Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

**Multiple Cover Finish Options:** Durable black powder coat and brushed stainless steel finishes blend with most decors.

**cULus Listed:** Meets UL US and Canadian Safety standards for Multioutlet Assemblies (File E15191, Guide PVGT).

## Specifications

### General Info

Product Line	Wiremold	Color	Black
UPC Number	786776186864	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Tamper-Resistant
Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Flip Up		

Dimensions

Product Weight US	3.35 lb	Internal Depth	3.25 in
-------------------	---------	----------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Cord Length	6 ft	Amperage	20 A
-------------	------	----------	------

Wiring Method	Hard-Wired	NEMA Configuration Code	5-20R
---------------	------------	-------------------------	-------

Mounting Type	Recessed	Cutout Shape	Rectangular
---------------	----------	--------------	-------------

Voltage	125.0 V
---------	---------