



Unit includes one (1) 20A black tamper-resistant duplex receptacle. Second opening will accept adapter for one (1) Wiremold CM Series Open System 2A module, one (1) Ortronics Series II or one (1) TracJack adapter to accommodate a wide range of communication outlets. Adapters are included in hardware bag. Unit comes with a 6' (1.83m) cord. Comes with a brushed stainless steel finish.

Features & Benefits

Sleek, Attractive Design: Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

Tamper-Resistant Receptacles: Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

New Soft Opening Cover Mechanism: Opening and closing the cover is quieter and easier with a more professional feel.

Expanded Configuration Options: Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

UL Spill Water Protection: Meets and exceeds UL1363 standard for relocatable power taps. Eliminates risk of shock or short circuiting due to moisture entering device.

USB Charging Capability: Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

Multiple Cover Finish Options: Durable black powder coat and brushed stainless steel finishes blend with most decors.

cULus Listed: Meets UL US and Canadian safety standards for Relocatable Power Taps (File E66421, Guide XBYS) and Multitoutlet Assemblies (File E15191, Guide PVGT).

Specifications

General Info

Product Line	Wiremold	Color	Stainless Steel
UPC Number	786776184945	Country Of Origin	Mexico
Number of Receptacles	1	Construction	Die Cast
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit

Standard	cULus Listed Relocatable Power Tap: File E66421 Guide XYBS, cULus Listed Multioutlet Assembly: File E15191 Guide PVGT, Meets Article 380 of NEC		Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Flip Up			
Dimensions				
Product Weight US	6.25 lb		Internal Depth	3.25 in
Listing Agencies / 3rd Party Agencies				
cULus ListingNumber	E66421		cULus Listed	Yes
Trade Programs				
USMCA	Yes			
Additional Information				
RoHS Compliant	Yes			
Technical Information				
Cord Length	6 ft		Amperage	20 A
Cable Entry	Below		Wiring Method	Cord-ended
NEMA Configuration Code	5-20R		Mounting Type	Recessed
Cutout Shape	Rectangular		Voltage	125.0 V