



Pass and Seymour
DR Series CFL/LED/Incandescent Single Pole/3-Way Rotary Dimmer, White
Part No. DRCL453PWCCV4



Features & Benefits

Convenient Operation - Combines ON/OFF Decorator style switch with separate slider for dimming control

Constant memory returns lights to previous level after a power failure

Sleek, ergonomic design that matches well with other decorator products Higher ratings

Single pole and 3-way operation

Screw-pressure-plate back wire terminals to save time, space and money

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007088786
Country Of Origin	China	Product Series	Decorator
Features	Lighted, Low-End Trim (Dim Range)	Switch Type	Rocker, Rotary, Single Pole 3-Way
Number of Switches	1	Application Sector	Residential
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
------------------	---------	------------------	---------

Product Height US4.19 in

Listing Agencies / 3rd Party Agencies

cULus ListedYes

Technical Information

Preset	Yes	Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Poles	Single Pole 3-Way	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Load Type	CFL, Halogen, Incandescent, LED		