



The DRD4 in-wall forward-phase dimmer operates most dimmable lighting types including incandescent, dimmable fluorescent, dimmable LED, dimmable cathode, and neon. As part of the RF Lighting Control System, it can be controlled from other devices located

Features & Benefits

Patented Top Dog RF communication protocol: 900 MHz radio

Patented overload and short circuit protection.

No control wiring necessary.

Large surface-mounted antenna ensures maximum broadcast coverage.

Stores room and house scenes.

Compatible with Decorator wall plates.

5-year warranty.

Note: Wall plate sold separately from device.

Specifications

General Info

Product Line	On-Q	UPC Number	754182916283
Country Of Origin	China	Application Sector	Residential
Standard	ANSI/UL 1472, CSA-C22.2 No. 184, FCC PART 15 B	Type	Dimmer

Technical Information

Amperage	5 A	Number of Poles	Single Pole
Wattage	600 W	Voltage	120 V