



On-Q  
14-inch Enclosure with Hinged Door  
Part No. EN1450



This 14" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

## Features & Benefits

14-in Enclosure with Hinged Door	Drywall depth indicators
Flush and surface installation	Mounting tabs provide correct flush-mount position for standard installations
Patented mounting system offers versatile module mounting options	Cover included
Made in the USA	

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428023036	Country Of Origin	United States
Package Quantity	1	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

Technical Information

Thickness	0.1 in	Enclosure Type	Traditional
Cable Entry	(6) rear knockouts, (3) top knockouts, (2) rectangular knockouts for 1-gang electrical box	Frame	Cold Rolled Steel