



On-Q
28-inch Enclosure, No Cover
Part No. EN2880



This 28" enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting.

Features & Benefits

Includes five openings on the top of the enclosure with knockouts

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Literature pouch included for dealer information

Includes self-adhesive cable identification table

Made in the USA

Specifications

General Info

| | | | |
|------------------|--|--------------------|---------------|
| Product Line | On-Q | Color | White |
| UPC Number | 804428023159 | Country Of Origin | United States |
| Package Quantity | 1 | Application Sector | Residential |
| Standard | UL (UL985, UL1023, UL1863), cULus, CSA, RoHS | Type | Enclosure |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 14.25 in | Product Depth US | 3.6 in |
| Product Height US | 28.0 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

Additional Information

| | |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

| | | | |
|-------------|--|----------------|-------------------|
| Thickness | 0.1 in | Enclosure Type | Traditional |
| Cable Entry | (6) rear knockouts,(3) top knockouts,(2) rectangular knockouts for 1-gang electrical box | Frame | Cold Rolled Steel |