



This 28" enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting.

Features & Benefits

- Flanged covers hide drywall openings
- Flush and surface installation
- Patented mounting system offers versatile module mounting options
- Includes self-adhesive cable identification table
- Drywall depth indicators
- Mounting tabs provide correct flush-mount position for standard installations
- Literature pouch included for dealer information
- Made in the USA

Specifications

General Info

UPC Number	804428023159
Country Of Origin	United States
Product Line	On-Q
Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
CSA Listed	Yes

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Cable Entry	(6) rear knockouts, (3) top knockouts, (2) rectangular knockouts for 1-gang electrical box in
Thickness	0.1 in

Frame

Cold Rolled Steel
