On-Q
28-inch Enclosure, No Cover
Part No. EN2880

This 28-inch enclosure is the perfect solution for a basic structured wiring system. Designed with larger top openings, it makes pulling wire easier and more efficient. The enclosure also features additional knockouts, more side lances, and side tabs, providing greater flexibility for mounting and installation.

Features & Benefits

- Includes five openings on the top of the enclosure with knockouts
- Flush and surface installation
- Patented mounting system offers versatile module mounting options
- Includes self-adhesive cable identification table
- Drywall depth indicators
- Mounting tabs provide correct flush-mount position for standard installations
- Literature pouch included for dealer information
- Made in the USA

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023159	Country Of Origin	United States
Material	Steel	Product Type	Wiring Enclosure
Application Sector	Residential	Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	28.0 in	Enclosure Size	28 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

Additional Information

RoHS Compliant	Yes

Technical Information

Thickness	0.1 in	Frame	Cold Rolled Steel