



On-Q  
28-inch Enclosure, No Cover  
Part No. EN2880



This 28-inch enclosure is the perfect solution for a basic structured wiring system. Designed with larger top openings, it makes pulling wire easier and more efficient. The enclosure also features additional knockouts, more side lances, and side tabs, providing greater flexibility for mounting and installation.

## Features & Benefits

Includes five openings on the top of the enclosure with knockouts

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Literature pouch included for dealer information

Includes self-adhesive cable identification table

Made in the USA

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428023159	Country Of Origin	United States
Application Sector	Residential	Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS
Type	Enclosure		

### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	28.0 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Thickness	0.1 in	Frame	Cold Rolled Steel
-----------	--------	-------	-------------------