



On-Q
42-inch Enclosure with Hinged Door
Part No. EN4250



Perfect for larger installations, this 42" enclosure features universal On-Q style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more s

Features & Benefits

42-in Enclosure with Hinged Door	Drywall depth indicators
Flush and surface installation	Mounting tabs provide correct flush-mount position for standard installations
Patented mounting system offers versatile module mounting options	Literature pouch included for dealer information
Includes self-adhesive cable identification table	Cover included
Made in the USA	

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023180	Country Of Origin	United States
Application Sector	Residential	Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS
Type	Enclosure		

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	42.0 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Thickness	0.1 in	Cable Entry	(6) rear knockouts
-----------	--------	-------------	--------------------

Frame	Cold Rolled Steel
-------	-------------------
