



Ortronics
EZ Patch™ Box, CAT6 9ft, Yellow, Qty 40
Part No. EZC609Q40-04



EZ Patch 40 pack, Clarity 6 modular patch cord, yellow, 9', Category 6, four-pair UTP stranded 24 AWG PVC/CM, center tuned with Clarity 6 connecting hardware for optimum Category 6 installed performance

Features & Benefits

Dispenses patch cords quickly and easily: Reduces staging and installation time

Eliminates trash from opening bags: A green, friendly approach to packaging patch cords

Provides a more orderly staging approach: Eliminates errors and tangles from traditional staging

Factory Tested and ETL third party tested and verified to TIA/EIA 568C.2

Par align 2 pair-positioning technology: Maintains pair integrity through the plug termination, allowing mating hardware to be designed/tuned to these cords

Snagless plug design: Protects plugs when pulling through pathways or cable managers

Premium conductor cordage: Reliable performance and durable cord life

Specifications

General Info

Product Line	Ortronics	Color	Yellow
UPC Number	662875897323	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Copper Patch Cord		

Dimensions

Product Width US	12.25 in	Product Depth US	12.25 in
Product Height US	12.5 in	Cable Length	9 ft

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Jacket Material	PVC	Operating Temperature Min	-10 °C
Category Performance Rating	Cat6	Wire Gauge	24 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
Jacket Application	Riser Rated	Bend Radius	0.88 in
Shielded/Unshielded	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Stranded	Operating Temperature Max	60 °C
Jacket Rating	CM Rated	Cable Diameter	0.22 in
Braid	Non-braided Wiring	Operating Temperature	-10°-60°C
Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C