



Ortronics
EZ Patch™ Flat Pack Clarity CAT6 5FT, 12 Pack, Blue
Part No. EZFPM605Q12-06



The EZ Patch Flat Pack is an innovative addition to the EZ Patch series, allowing a 12 or 24-pack of cords to be distributed from flat plastic packaging, which is ideal for patch panel applications. Available in CAT6 & CAT6A

Features & Benefits

Bulk packaging: Reduces installation time and packaging waste. No dealing with individual bags or zip ties.

No cord memory: Packs are laid out flat in a bundle

Plastic packaging: Ideal for data center applications that do not allow cardboard

Light weight design: Installers can easily carry the bag over their shoulder.

Easy tear perforation strips: Tears at each end allow for quick connection or easy removal of cords.

Cable management: Bag can be used as a fishing mechanism to route a bundle through a vertical manager.

Packaged in 12 or 24 packs: Quantities ideal for patch panel applications.

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875031529	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Copper Patch Cord		

Dimensions

Product Length US	5.0 FT	Cable Length	5 ft
-------------------	--------	--------------	------

Additional Information

Product Environmental Profile Yes

Technical Information

Jacket Material	PVC	Operating Temperature Min	-10 °C
Category Performance Rating	Cat6	Wire Gauge	24 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
Jacket Application	Riser Rated	Bend Radius	0.88 in
Shielded/Unshielded	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Stranded	Operating Temperature Max	60 °C
Jacket Rating	CM Rated	Cable Diameter	0.22 in
Braid	Non-braided Wiring	Operating Temperature	-10°-60°C
Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C