



Ortronics
EZ Patch™ Flat Pack Reduced Diameter CAT6 9ft, 12 Pack, Blue
Part No. EZFPR609Q12-06



"The EZ Patch™ Flat Pack is an innovative addition to the EZ Patch series, allowing 12 or 24 pack cords to be distributed from flat plastic packaging, which is ideal for patch panel applications or installations on the go.

Features & Benefits

Bulk packaging: Reduces installation time and packaging waste. No dealing with individual bags or zip ties.

No cord memory: Packs are laid out flat in a bundle

Plastic packaging: Ideal for data center applications that do not allow cardboard

Light weight design: Installers can easily carry the bag over their shoulder.

Easy tear perforation strips: Tears at each end allow for quick connection or easy removal of cords.

Cable management: Bag can be used as a fishing mechanism to route a bundle through a vertical manager.

Packaged in 12 or 24 packs: Quantities ideal for patch panel applications.

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875009146	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Copper Patch Cord		

Dimensions

Product Length US	9.0 FT	Cable Length	9 ft
-------------------	--------	--------------	------

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Jacket Material	PVC	Operating Temperature Min	-10 °C
Category Performance Rating	Cat6	Wire Gauge	28 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
Jacket Application	Riser Rated	Bend Radius	0.15 in
Shielded/Unshielded	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Stranded	Operating Temperature Max	60 °C
Jacket Rating	CMR Rated	Cable Diameter	0.6 in
Braid	Non-braided Wiring	Operating Temperature	-10°-60°C
Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C