



Pass and Seymour
Tamper-Resistant Floor Box Assembly - Two Gang for Wood Sub-Floors, Brass
Part No. FB2TRDRKS4B



Tamper-Resistant Floor Box Assembly, Dual-voltage. Two #8 duplex openings, Four threaded screw plugs. Includes 3232 15A, 125A tamper-resistant duplex receptacle, Cat5E Jack, F-connector, Ten Blanks and a low-voltage divider. Brass. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.	Rugged diecast cover plates with durable nickel or brass finish.
Meets UL514(c) and NEC 314.27(c) requirements including scrub water for tile floors.	Scrub water compliant without caulking, supplied with foam gasket and O-ring-equipped plugs.
Large box flange rests on finished floor -- no adjustments needed.	Swing brackets mounting, great for tile floors -- eliminates drilling for mounting screws.
Extra-deep design leaves plenty of wiring room.	Includes 15 Amp, 125 Volt tamper-resistant duplex receptacle, low-voltage divider, Cat 5e jack, F-connector, and blanks.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
Country Of Origin	Mexico	Construction	Wood Floor
Application Sector	Residential/Commercial	Standard	UL Listed

Dimensions

Cubic Capacity	42.5 cu in
----------------	------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Number of Outlets	2
---------------------	-----	-------------------	---
