



FC062LB: Standard Duty, Closed Mesh, Locking Bale (Universal Eye), Cable Diameter 0.62 - 0.74 inches, Bale Length 18-in, Mesh Length 11-in, Break Strength 1150 lbs.

Features & Benefits

| | |
|---|---|
| Closed mesh support grips are used when the end of the cable is accessible. | Standard duty closed mesh support grips are designed for loads up to 600 lbs. |
| Vertical runs of no more than 100 ft. | They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing. |
| Support grips are woven of corrosion-resistant tinned-stainless steel wire. | Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information. |
| Bale Length: 18: Mesh Length: 11 | |

Specifications

General Info

| | | | |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Support and Strain Relief Grips, Various Types of Pulling | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 67507 |
|------------|-----|-----------------|-------|

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 0.62 in | Minimum Cable Range | 0.74 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Approx. Break Strength: 1150 | | |