



Pass and Seymour  
**Flexcor® Support Grips Standard Duty, Closed Mesh, Single-Eye Grip, Cable Diameter 0.75 - 0.99 in.**  
Part No. FC075U



FC075U: Standard Duty, Closed Mesh, Single-Eye Grip, Cable Diameter 0.75 - 0.99 inches, Bale Length 8-in, Mesh Length 14-in, Break Strength 1300 lbs.

## Features & Benefits

Closed mesh support grips are used when the end of the cable is accessible.

Standard duty closed mesh support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 8: Mesh Length: 14

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007980684
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Dimensions

Product Width US	0.99 in	Product Length US	13.0 in
------------------	---------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

### Technical Information

Maximum Cable Range	0.75 in	Minimum Cable Range	0.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations