



Pass and Seymour
Flexcor® Support Grips Standard Duty, Closed Mesh, Offset Eye Grips, Cable Diameter 1.25 - 1.49 in.
Part No. FC125OF



FC125OF: Standard Duty, Closed Mesh, Offset Eye Grips, Cable Diameter 1.25 - 1.49 inches, Bale Length 5-in, Mesh Length 16-in, Break Strength 1680 lbs.

Features & Benefits

Closed mesh support grips are used when the end of the cable is accessible.

Standard duty closed mesh support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 5: Mesh Length: 16

Specifications

General Info

| | | | |
|--------------------|----------------|--------------|---|
| Product Line | Pass & Seymour | UPC Number | 785007980370 |
| Country Of Origin | Mexico | Construction | Support and Strain Relief Grips, Various Types of Pulling |
| Application Sector | Industrial | Standard | UL/CSA Approval (consult factory) |

Dimensions

| | | | |
|------------------|---------|-------------------|---------|
| Product Width US | 1.49 in | Product Length US | 15.5 in |
|------------------|---------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 67507 |
|------------|-----|-----------------|-------|

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 1.25 in | Minimum Cable Range | 1.49 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |