



FC1500F: Standard Duty, Closed Mesh, Offset Eye Grips, Cable Diameter 1.50 - 1.74 inches, Bale Length 5-in, Mesh Length 18-in, Break Strength 1680 lbs.

## Features & Benefits

Closed mesh support grips are used when the end of the cable is accessible.

Standard duty closed mesh support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 5: Mesh Length: 18

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007980387
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Support Grip		

### Dimensions

Product Width US	1.74 in	Product Length US	17.0 in
Mesh Length	17 in	Cable Diameter Range	1.50-1.74 in

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

### Technical Information

Mesh Type	Closed	Approximate Break Strength	1540 lb
Maximum Cable Range	1.5 in	Eye Style	Offset
Minimum Cable Range	1.74 in	Capacity	Various Cable Diameter Ranges

---

Indoor/Outdoor

Both

Mounting

Consult the Factory for Mounting  
Recommendations

---