



Pass and Seymour
Flexcor® Support Grips Standard Duty, Closed Mesh, Double -Eye Grip, Cable Diameter 1.75 - 1.99 in.
Part No. FC175UU



FC175UU: Standard Duty, Closed Mesh, Double -Eye Grip, Cable Diameter 1.75 - 1.99 inches, Bale Length 6-in, Mesh Length 20-in, Break Strength 3150 lbs.

Features & Benefits

| | |
|---|---|
| Closed mesh support grips are used when the end of the cable is accessible. | Standard duty closed mesh support grips are designed for loads up to 600 lbs. |
| Vertical runs of no more than 100 ft. | They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing. |
| Support grips are woven of corrosion-resistant tinned-stainless steel wire. | Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information. |
| Bale Length: 6: Mesh Length: 20 | |

Specifications

General Info

| | | | |
|--------------------|----------------|--------------|---|
| Product Line | Pass & Seymour | UPC Number | 785007981056 |
| Country Of Origin | Mexico | Construction | Various Types of Pulling, Support and Strain Relief Grips |
| Application Sector | Industrial | Standard | UL/CSA Approval (consult factory) |

Listing Agencies / 3rd Party Agencies

| | |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 1.75 in | Minimum Cable Range | 1.99 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |