



FC22GL: Extra-Hard Use, Closed Mesh, Cable Diameter 0.22 - 0.32 inches, Mesh Length 4.5-in

Features & Benefits

EHU wire mesh grips provide additional strain-relief for wiring device plugs and connectors used on portable equipment in commercial and institutional applications, and industrial plant and construction site areas, which incur abnormally high abuse. Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information. Mesh Length: 4.00

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Dimensions

Product Width US	0.32 in	Product Depth US	4.5 in
Product Height US	0.32 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Maximum Cable Range	0.22 in	Minimum Cable Range	0.32 in
---------------------	---------	---------------------	---------

Capacity

Various Cable Diameter Ranges

Mounting

Consult the Factory
for Mounting
Recommendations

Load

Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.
