



Pass and Seymour  
**Flexcor® Support Grips Heavy Duty, Double-Eye, Cable Diameter 0.75 - 0.99 in.**  
Part No. FCHL075UU



FCHL075UU: Heavy-Duty, Closed Mesh, Double-Eye, Cable Diameter 0.75 - 0.99 inches, Bale Length 10-in, Mesh Length 26-in, Break Strength 2700 lbs.

## Features & Benefits

Heavy-duty support grips feature a double weave mesh and are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing. Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 10: Mesh Length: 26

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007981445
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Technical Information

Maximum Cable Range	0.75 in	Minimum Cable Range	0.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations