



Pass and Seymour
Flexcor® Support Grips Heavy Duty, Double-Eye, Cable Diameter 1.50 - 1.99 in.
Part No. FCHL150UU



FCHL150UU: Heavy-Duty, Closed Mesh, Double-Eye, Cable Diameter 1.50 - 1.99 inches, Bale Length 10-in, Mesh Length 35-in, Break Strength 4720 lbs.

Features & Benefits

Heavy-duty support grips feature a double weave mesh and are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 10: Mesh Length: 35

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007981476
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Support Grip		

Dimensions

Mesh Length	17 in	Cable Diameter Range	1.50-1.74 in
-------------	-------	----------------------	--------------

Technical Information

Approximate Break Strength	4490 lb	Maximum Cable Range	1.5 in
Eye Style	Double	Minimum Cable Range	1.99 in

Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
Mounting	Consult the Factory for Mounting Recommendations		