



Pass and Seymour
Flexcor® Support Grips Standard Duty, Split Rod, Double-Eye, Cable Diameter 0.50 - 0.61 in.
Part No. FR050UU



FR050UU: Standard Duty, Split Rod, Double-Eye, Cable Diameter 0.50 - 0.61 inches, Bale Length 4-in, Mesh Length 11-in, Break Strength 770 lbs.

Features & Benefits

- Split rod support grips are used when the end of the cable cannot be easily accessed and the installation is temporary.

Vertical runs of no more than 100 ft.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Bale Length: 4: Mesh Length: 11
- Split rod support grips are designed for loads up to 600 lbs.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007983180
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Support Grip		

Dimensions

Mesh Length	8.5 in	Cable Diameter Range	0.500-0.620 in
-------------	--------	----------------------	----------------

Technical Information

Mesh Type	Split Rod	Approximate Break Strength	790 lb
Maximum Cable Range	0.5 in	Eye Style	Double
Minimum Cable Range	0.61 in	Capacity	Various Cable Diameter Ranges
Indoor/Outdoor	Both	Mounting	Consult the Factory for Mounting Recommendations