



Pass and Seymour Support Grips Standard Duty, Split Rod Part No. FR100LB

Standard-duty, Split rod, Locking bale (Universal eye). Cable diameter - 1.000-1.240", Bale length - 14", Mesh length - 13", Break strength - 1,920 lbs.



Features & Benefits

Split rod support grips are designed for loads up to 600 lbs.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-bronze wire.

Vertical runs of no more than 100 ft.

Split rod support grips are used when the end of the cable cannot be easily accessed and the installation is temporary.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

UPC Number	785007982220	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Construction	Various Types of Pulling, Support and Strain Relief Grips	Standard	UL/CSA Approval (consult factory)

Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	Cable Dia. Range: 1.000-1.240; Bale Length: 14; Mesh Length: 13
Capacity	Various Cable Diameter Ranges	Load	Approx. Break Strength: 1,920