



FS250U: Standard Duty, Split Lace, Single Eye, Cable Diameter 2.50 - 2.99 inches, Bale Length 18-in, Mesh Length 24-in, Break Strength 3760 lbs.

Features & Benefits

- Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation.
- Split lace support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Support grips are woven of corrosion-resistant tinned-stainless steel wire.
- Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.
- Bale Length: 18: Mesh Length: 24

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	2.5 in	Minimum Cable Range	2.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 3760		