



Pass and Seymour  
**Flexcor® Support Grips Standard Duty, Split Lace, Single Eye, Cable Diameter 3.50 - 3.99 in.**  
Part No. FS350U

FS350U: Standard Duty, Split Lace, Single Eye, Cable Diameter 3.50 - 3.99 inches, Bale Length 24-in, Mesh Length 28-in, Break Strength 5040 lbs.



## Features & Benefits

Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation.

Vertical runs of no more than 100 ft.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Bale Length: 24: Mesh Length: 28

Split lace support grips are designed for loads up to 600 lbs.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007984279
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Technical Information

Maximum Cable Range	3.5 in	Minimum Cable Range	3.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations