



FSHL200UU: Heavy-Duty, Split Lace, Double-Eye, Cable Diameter 2.00 - 2.49 inches, Bale Length 10-in, Mesh Length 37-in, Break Strength 10080 lbs.



Features & Benefits

- Heavy-duty support grips feature a double weave mesh and are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Support grips are woven of corrosion-resistant tinned-stainless steel wire.
- Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.
- Bale Length: 10: Mesh Length: 37

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007984996
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Maximum Cable Range	2 in	Minimum Cable Range	2.49 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations