



FSHL300UU: Heavy-Duty, Split Lace, Double-Eye, Cable Diameter 3.00 - 3.49 inches, Bale Length 10-in, Mesh Length 41-in, Break Strength 10080 lbs.



## Features & Benefits

Heavy-duty support grips feature a double weave mesh and are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 10: Mesh Length: 41

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007985016
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Support Grip		

### Dimensions

Mesh Length	31 in	Cable Diameter Range	3.00-3.49 in
-------------	-------	----------------------	--------------

### Technical Information

Approximate Break Strength	13420 lb	Maximum Cable Range	3 in
Eye Style	Double	Minimum Cable Range	3.49 in
Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
Mounting	Consult the Factory for Mounting Recommendations		