Wattstopper
0-10V PIR in FIXTURE SENSOR BL E120-277V
Part No. FSP-311

The FSP-3x1 sensors provide continuous dimming intensity control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via the iOS or Android Sensor Configuration App capable of storing and transmitting unlimited sensor profiles. The FSP-3x1 family is available in three different voltage configurations adding flexibility to your fixture design or project.

Features & Benefits

- Designed for LED fixtures and rated for extreme temperatures
- Hold off setpoint with automatic calibration option for convenience and added energy savings
- Adjustable via the iOS® or Android® Sensor Configuration App
- Adjustable time delay and cutoff delay
- Fully adjustable high and low dimmed light levels
- Continuous dimming for Energy Code Compliance
- Choice of four lenses for mounting heights from 8 ft. to 40 ft.

Specifications

General Info

Product Line	Wattstopper	UPC Number	754182943685
Country Of Origin	China		

Additional Information

RoHS Conformant	Yes	Security	Yes

Technical Information

Sensor Type	Daylight, Occupancy