



5' Plugmold Tamper-Resistant Multioutlet System

Features & Benefits

Meets new Tamper Resistant requirements for 2008 NEC Section 406.11. Provides additional protection from burns and other injuries. Mandated for residential applications.

Available in 3' & 5' [914mm & 1.5m] lengths with 6" [305mm] receptacle spacing. Provides additional power access in smaller, more confined areas. Multiple lengths present more mounting options.

Steel or aluminum construction. Superior strength for residential applications. Providing years of protection and convenience.

Multiple finishes. Available in ivory, gray, white, black, stainless steel and anodized aluminum to accommodate a wide range of applications.

Custom options available. Custom configurations and finish options are also available. Consult the factory for more information.

This product meets the material restrictions of RoHS.

Built-in shutter system. Prevents the insertion of unwanted objects such as hairpins, keys and nails. Providing additional protection for occupants including small children.

15A Proprietary Simplex Decorator Receptacle. Functional and aesthetically pleasing, matches any décor.

Designed for surface mounting. Easier and more convenient installation. Eliminates the need to break through walls.

Multiple power feed options. Provide clean, attractive installations with concealed power sources.

cULus Listed.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776174830
Country Of Origin	United States	Number of Receptacles	10

Application Sector	Commercial	Standard	cULus Listed Raceway: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover: Meets Article 386 of NEC. Plugmold Strips: Meets Article 380 & 406.11 of NEC.
Type	Plugmold		
Dimensions			
Product Width US	1.3 in	Product Depth US	0.75 in
Product Length US	1.3 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Buy American Act Compliance			
NAFTA	Yes		
Additional Information			
RoHS Conformant	Yes	Product Environmental Profile	Yes
Technical Information			
Amperage	15 A	Enclosure Type	Steel
Voltage	125.0 V	Environmental Conditions	Dry interior locations