



Wiremold  
20GB606 Steel Plugmold® Multioutlet System  
Part No. G20GB606



6' Plugmold Multioutlet System with 12 single outlets

## Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

This product meets the material restrictions of RoHS.

## Specifications

### General Info

Product Line	Wiremold	Color	Gray
UPC Number	786776091861	Country Of Origin	United States
Product Series	2000 Series	Number of Receptacles	12

		cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover & Plugmold Series w/Snapicoil Haarness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. cULus Listed Raceway: File E4376 Guide RJBT. Fittings: File E41751 Guide RJPR. Base & Black Cover: Meets Article 386 of NEC. Meets Section 12-600 of CEC.	
Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail	Standard	
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Plugmold
Installed Devices	Single Receptacle		
Dimensions			
Product Width US	1.3 in	Product Weight US	3.78 lb
Product Depth US	0.75 in	Product Length US	1.3 in
Receptacle Spacing	6 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes

Trade Programs

USMCA                      Yes

Additional Information

RoHS Compliant                      Yes                      Product Environmental Profile    Yes

Technical Information

Is Pre-Wired                      Yes                      Wiring Configuration                      Single Circuit

Amperage                      15 A                      Indoor/Outdoor                      Indoor

Wiring Method                      Hard-Wired                      NEMA Configuration Code                      5-15R

Mounting Type                      On Surface                      Voltage                      125.0 V

Environmental Conditions    Dry interior locations