



Quiktron

DO NOT USE Cisco® GLC-FE-100FX-RGD Compatible 100Base-FX MMF SFP (mini-GBIC) Transceiver Module
Part No. GLCFE100FXRGDLEG

This Cisco GLC-FE-100FX-RGD compatible SFP transceiver provides 100Base-FX throughput up to 2km over multi-mode fiber (MMF) at a wavelength of 1310nm using a LC connector. It is also capable of withstanding rugged environments and can operate at temperatures between -40°C to +85°C. Our transceiver is guaranteed to be 100% compatible with the equivalent Cisco transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. It is built to meet or exceed the specifications of Cisco, as well as to comply with multi-source agreement (MSA) standards to ensure seamless network integration.

Specifications

General Info

Product Line	TBD	Color	Silver
Country Of Origin	United States	Application Sector	Commercial/Industrial
Type	Transceiver		

Additional Information

Product Has Potential to Contribute to LEED	Yes
---	-----