



Infinium HDFP Adapter Panels offer pass through connections and front-loading access. The compact design optimizes space and features fiber port labeling for easier identification. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

Available in 6 & 8 MPO configurations

Aqua, Green, Gray & Beige adapter color options

Supports up to 384 fibers in a 1RU Infinium series enclosures.

Made of durable polycarbonate

Specifications

General Info

Product Line	Ortronics	Color	White
UPC Number	662875025511	Country Of Origin	Mexico
Included	Cover	Application Sector	Commercial, Data Center
Warranty Type	5-Year	Type	Adapter Panel

Dimensions

Product Width US	4.19 in	Product Depth US	0.8 in
Product Height US	1.24 in		

Technical Information

Fiber Optic Cable Type	OM4	Operating Temperature Min	-10 °C
Compatibility	M4/HDFP	Number of Ports	96
Operating Temperature Max	60 °C	Shuttered Adapters	Yes

Single/Multimode	Multimode	Connector 2	LC Female
Connector 1	LC Female	Operating Temperature	-10°-60°C
Operating Humidity	0-80% RH (Non-Condensing)		