Ortronics

HDFM Fiber Module with HiLOC Boot, Simplex, SC, Aqua

Part No. HDHFM-FSC1CL-00

HDFM Fiber Modules with integrated HiLOC mounting foot are feed through fiber optic adapter modules that support high density applications by adding 0U patching capability outside of the rack or cabinet. These modules provide superior cable strain relief for routing in mounting accessories such as in the Universal Cable Trough, Multi-Use Panel integrated with Cablofil Tray, the MM20 HiLOC Cable Management Disk.

Features & Benefits

The Multi-Use Panel snaps securely into Mighty Mo vertical managers and Cablofil cable tray

Tool less integration

ZeroU solution

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875797289	Country Of Origin	Mexico
Material	Thermoplastic	Product Type	Jack
Features	HDJ Design, Rear Loading	Included	Cover
Application Sector	Commercial, Data Center	Standard	TIA-568-C.3;RoHS Compliant
Warranty Type	5-Year		

Dimensions

Product Width US	0.62 in	Product Depth US	1.06 in
Product Height US	1.1 in		

Technical Information

Fiber Optic Cable Type	OM3, OM4, OS2	Operating Temperature Min	-10 °C
Compatibility	HiLOC	Number of Ports	1
Alignment Sleeve Material	Zirconia	Simplex/Duplex	Simplex
Polarity Type	Universal	Operating Temperature Max	60 °C
Single/Multimode	Multimode	Number of Fibers	1
Connector 2	SC	Connector 1	SC
Operating Temperature	-10°-60°C	Durability	500 matings
Operating Humidity	0-80% RH (Non-Condensing)	Connectivity Footprint	HiLOC
Storage Temperature	-40° - 75° C		