



High density jack module provides a single F-connector coupler F/F with under .2dB of insertion loss at 2GHz (1/3 the loss of standard models). HDJ is a versatile single jack solution in a easy mount rear load footprint which allows a choice of up to six jacks/connectors to fit in a single gang plate, also mountable in HDJ panels.

Features & Benefits

Rear Loading

High Density Jack Footprint

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875373285	Country Of Origin	Taiwan, Province Of China
Material	Plastic	Application Sector	Commercial, Industrial
Standard	UL Standard	Warranty Type	5-Year
Type	Jack		

Dimensions

Product Width US	0.62 in	Product Depth US	1.61 in
Product Height US	0.74 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Frequency Rating	3 GHz	Connector 2	F-Type Male
Connector 1	F-Type Female	Impedance	75 Ohm
Connectivity Footprint	TechChoice		
