



radiant Collection  
radiant® Multi-Location Remote Dimmer, White  
Part No. HMRWCCV4



Provides precise dimming control of a light or fixture from another part of the room through this second on-wall controller. Must be used with the Multi-Location Master Dimmer. Part of the radiant® Collection, it also features clean lines and smooth control for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

- Installs easily with 3-way wiring for multi-location dimming. For use with most Incandescent, CFL/LED (with the exception of 0 - 10v options) and MLV dimmable bulbs.
- Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.
- Constant memory features returns lights to their previous level after a power failure or outage.
- No derating required in multi-gang applications.
- Features durable, high-impact resistant thermoplastic construction.
- More color options available. (For Tri-Color version: Includes three interchangeable face plates in white, light almond, and ivory for flexible customization.)
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                   |                           |                    |                  |
|-------------------|---------------------------|--------------------|------------------|
| Product Line      | Pass & Seymour            | Color              | White            |
| Country Of Origin | China                     | Features           | Indicator Lights |
| Switch Type       | Paddle                    | Number of Switches | 1                |
| Warranty Type     | Limited Lifetime Warranty |                    |                  |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 1.75 in | Product Depth US | 1.25 in |
|------------------|---------|------------------|---------|

|                   |         |
|-------------------|---------|
| Product Height US | 4.25 in |
|-------------------|---------|

Technical Information

|                    |                        |                 |                                    |
|--------------------|------------------------|-----------------|------------------------------------|
| Number of Gangs    | 1                      | Amperage        | 15 A                               |
| Bulb Compatibility | CFL, Incandescent, LED | Number of Poles | 3-Way, Multi-Location, Single Pole |
| Wattage            | 700 W                  | Mounting Type   | Box                                |
| Voltage            | 120.0 V                |                 |                                    |