



The Mini Pass-Through Grommet is an in-wall cable management solution meant for speed!

The mini Pass-Through grommets hide low voltage cables in the wall and out of sight. Utilizing a 2-inch hole saw (not included), cut an opening in the ceiling or wall, run cabling and secure the mini Pass-Through grommets in under 20 min. The Mini Pass-Through grommet features wing clamps that engage behind the drywall to prevent slippage or fall out. This grommet is capable of supporting up to four low voltage cables and is ideal for HDMI, TV cabling, IP Cameras, wireless access points, and wall-mounted speakers.

Features & Benefits

Hide low voltage cables in the wall and out of sight

Installs in under 20 minutes

Secures to wall or ceiling with old work wing clamps

Requires a 2 in. Hole Saw (not included) and supports up to 4 low voltage cables in a small footprint

Ideal for HDMI and TV Cables, IP Cameras, Wireless access points, and wall mounted speakers.

Contents include: 4 Mini Pass-Through Grommets and Instruction sheet.

Specifications

General Info

| | | | |
|--------------|----------------------------------|-----------------------|---------------------------------|
| Product Line | On-Q | Color | White |
| Finish | Matte | Country Of Origin | China |
| Construction | Plastic and Rubber | Installation Location | In-Wall |
| Standard | Class 2 Low Voltage Cable Access | Warranty Type | Manufacturer's Limited Warranty |
| Type | Grommet | | |

Dimensions

| | | | |
|-------------------|---------|-------------------|---------|
| Product Width US | 2.45 in | Product Weight US | 0.06 lb |
| Product Depth US | 2.45 in | Product Height US | 1.35 in |
| Product Length US | 2.45 in | | |

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

RoHS Conformant Yes

Technical Information

| | | | |
|---------------------|----|--------------------------|-----------------------------------|
| Is Tamper-Resistant | No | Cable Entry | 2 in |
| Number of Holes | 1 | Environmental Conditions | Not intended for fire-rated walls |