



Isolated Ground Quad Receptacle 20amp 125volt Orange

Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Shielding walls guard against live-circuit-to-ground shorts.

UL and CSA listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Built-in wire stripping gauge.

Heavy-duty, phosphor bronze contacts.

Split circuit break-off tabs.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color Orange

UPC Number 785007125658

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Residential/Commercial

Standard UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

CSA Listed Yes

CSA File Number 16063

Technical Information

Number of Poles Double Pole

Voltage 125 V

Temperature Rating Operating Temperature: -40°C to +65°C [-40°F to 150°F] continuous without impact

Wire Size #14 - #12

Number of Wires 3

Environmental Conditions Flammability: UL94 V2 and UL94-5 VA
