



Wiremold
Rack Mount 120V/20A/6 rear O/L /lighted switch/6' cord
Part No. J06B0B20

Six rear 20A outlets, on/off switch, 6' (1.8m) cord. Receptacle center-to-center 1 1/2" (38mm).



Features & Benefits

Six rear 20A outlets, 6' (1.8m) cord. Receptacle center-to-center 1 1/2" (38mm).

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776542158	Country Of Origin	Mexico
Material	Steel	Product Series	Rack Mount
Receptacle Type	Simplex	Number of Receptacles	6
Application Sector	Commercial, Residential	Standard	cULus Recognized: File E66421, Guide XBYS2 XUHT2 VZCA2
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC

Dimensions

Product Width US	1.75 in	Product Weight US	3.5 lb
Product Depth US	2.57 in	Product Length US	19.0 in
Receptacle Spacing	1.5 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Trade Programs

USMCA Yes

Technical Information

Phase	Single	Cord Length	6 ft
Amperage	20 A	Enclosure Type	Steel
Indoor/Outdoor	Indoor	Wiring Method	Cord-ended
NEMA Configuration Code	5-20P, 5-20R	Mounting Type	Rack Mounting
Location Rating	Dry	Voltage	125.0 V
Environmental Conditions	Dry interior locations		
