



Wiremold
Rack Mount 120V/15A/6 rear O/L/15' cord
Part No. J06B2BX

Six rear outlets, 15A, 15' (4.6m) cord. Receptacle center-to-center 1 1/2" (38mm).



Features & Benefits

Six rear outlets, 15A, 15' (4.6m) cord. Receptacle center-to-center 1 1/2" (38mm).

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776104158	Country Of Origin	Mexico
Material	Steel	Product Series	Rack Mount
Receptacle Type	Simplex	Number of Receptacles	6
Application Sector	Commercial, Residential	Standard	cULus Recognized: File E66421, Guide XBYS2 XUHT2 VZCA2
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC

Dimensions

Product Width US	1.75 in	Product Weight US	4.0 lb
Product Depth US	2.57 in	Product Length US	19.0 in
Receptacle Spacing	1.5 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Phase Single Cord Length 15 ft

Amperage 15 A Enclosure Type Steel

Indoor/Outdoor Indoor Wiring Method Cord-ended

NEMA Configuration Code 5-15P, 5-15R Mounting Type Rack Mounting

Location Rating Dry Voltage 125.0 V

Environmental Conditions Dry interior locations
