



Wiremold
Rack Mount 120V/15A/2 front O/L, 4 rear O/L /lighted switch/6' cord
Part No. J24B0B

Two front, four rear outlets, lighted switch, 15A, 6' (1.8m) cord.
Receptacle center-to-center 1 1/2".



Features & Benefits

Two front, four rear outlets, lighted switch, 15A, 6' (1.8m) cord. Receptacle center-to-center 1 1/2".

Specifications

General Info

| | | | |
|-----------------------|--|--------------------|--------------|
| Product Line | Wiremold | UPC Number | 786776047905 |
| Country Of Origin | Mexico | Receptacle Type | Simplex |
| Number of Receptacles | 6 | Application Sector | Commercial |
| Standard | cULus Recognized: File E66421, Guide XBYS2 XUHT2 VZCA2 | Type | PIOC |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.75 in | Product Depth US | 2.57 in |
| Product Length US | 19.0 in | | |

Buy American Act Compliance

| | |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

| | |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

| | | | |
|--------------------------|------------------------|------------------|---------|
| Phase | Single | Frequency Rating | 60 Hz |
| Amperage | 15 A | Enclosure Type | Steel |
| Mounting Type | Rack Mounting | Voltage | 125.0 V |
| Environmental Conditions | Dry interior locations | | |
