



Wiremold
Rack Mount 120V/20A/2 front O/L, 4 rear O/L /lighted switch/15' cord
Part No. J60B2B20



Six front 20A outlets, on/off switch, 15' (4.6m) cord. Receptacle center-to-center 1 1/2" (38mm).

Features & Benefits

Six front 20A outlets, on/off switch, 15' (4.6m) cord. Receptacle center-to-center 1 1/2" (38mm).

Specifications

General Info

Product Line	Wiremold	UPC Number	786776542202
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	6	Application Sector	Commercial
Standard	cULus Recognized: File E66421, Guide XBYS2 XUHT2 VZCA2	Type	PIOC

Dimensions

Product Width US	1.75 in	Product Depth US	2.57 in
Product Length US	19.0 in		

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Phase	Single	Frequency Rating	60 Hz
Amperage	20 A	Enclosure Type	Steel
Mounting Type	Rack Mounting	Voltage	125.0 V
Environmental Conditions	Dry interior locations		
