



Cord-ended with black, flush cover. Unit comes with two 20A gasketed prewired receptacles with a 12' (3.65m) 14/3 SJT black cord. Includes adapter for Ortronics Series II and TracJack inserts. Communication modules sold separately.

## Features & Benefits

Hinged lid. Provides access to make connections and can be closed during use making the portal unobtrusive.	Finish options. Choose the finish of the flip-top lid.
Cover options. Choose either flush or contoured. Both options are available with a decorative, recessed area that can accept a wide range of laminates and veneers.	Configurable. Choose the communications requirements from the latest UTP to video and fiber optics.
Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point of use	Gasketed Receptacle. 15A spec grade receptacle is dust and moisture resistant.*
Installation flexibility. Unit is plug-ended or field-installable.	Flush. When closed, the unit does not interfere with the worksurface.
Listed to U.S. and Canadian safety standards.	

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776161151
Country Of Origin	United States	Construction	Aluminum
Application Sector	Commercial	Standard	cULus Listed Relocatable Power Tap: File E66421 Guide XYBS, cULus Listed Multioutlet Assembly: File E15191 Guide PVGT, Meets Article 380 of NEC
Type	Table Box		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Mounting Type	Recessed	Number of Outlets	2